

## CuMask+[TM] quality assured

A spokesman for the Innovation and Technology Bureau said that the quality of CuMask+™ is assured. All masks have been sterilised with ozone before they are packed.

"The manufacturer responsible for the mass production of CuMask+™ is certified to the ISO 9001 quality management system. Quality control is in place during production. Should any defect or stain be found in the process, the masks produced will not pass the quality requirement," the spokesman said yesterday (May 19).

To ensure hygiene, masks should be properly handled after open. CuMask+™ should be rinsed with clean water and soap every day. The filter layer needs not be detached while washing. Do not twist, wring, iron or tumble-dry CuMask+™. Lay flat until it is thoroughly dry before putting it away.